



39 CLINICAL EVALUATORS

1191 TOTAL USES

96% CLINICAL RATING

Key features: Next generation of **3M™ Scotchbond™ Universal Adhesive**

- Single bottle universal adhesive and primer for all dental materials; covers all direct and indirect bonding indications


Description

3M™ Scotchbond™ Universal Plus Adhesive is a light-cured, single-component dental adhesive:

- Next generation of **3M™ Scotchbond™ Universal Adhesive**
- The first radiopaque, universal adhesive available on the market
- Compatible with light-, dual-, and self-cured composite materials, cements, and core-build-up materials
- Can be used with self-etch, selective-etch, and total-etch techniques

Indications

- Bonding of light-, dual-, and self-cured composite or compomer restorations
- Root surface desensitization
- Bonding of pit and fissure sealants
- Protective varnish for glass ionomer restorations
- Repair of composite and compomer restorations
- Sealing of cavity preparations prior to amalgam placement

**Unique Attributes**

- First radiopaque universal adhesive
- Bonds and seals caries-affected dentin, supporting minimally invasive preparations
- BPA and BisGMA free
- High bond strength to etched glass ceramic; equivalent to silane
- No dual cure activator needed

**Clinical Tips**

- Gently air dry until adhesive layer appears glossy and uniform
- Treat it similar to **3M™ Scotchbond™ Universal Adhesive**

"IT HANDLED JUST LIKE SCOTCHBOND UNIVERSAL AND I LOVE THE RADIOPAQUE FEATURE."

Evaluators' Comments

"It did not run all over the tooth when being air dried - it stayed where I put it."

"After drying, it was easy to tell if you have a nice layer of material over the entire surface to be bonded."



"The re-designed bottle delivers a very small amount at a time."

"I did not experience any post-op sensitivity."

"You can use it with many more bonding procedures without the need for a separate activator."

"I like its slightly thicker consistency. This gives me the feeling that I am properly coating the cavity preparation."

"Can pool at line angles if you don't thoroughly air dry."

Evaluation Summary:**Compared to Competitive Products:****Consultants who would:**

100% Recommend to a colleague

Consultants who would want to stock in office:

41% Yes, instead of current product

43% Yes, in addition to current product

14% No, however I might want to order it for certain cases